



CrushBox DB-50PRO-E

Hard Drive destroyer for professional use.

HARD DRIVE DESTRUCTION

Physical Destruction

The safest and surest way to sanitize a hard drive is to physically destroy it. This is an attractive option if the drive is to be discarded anyway and not reused. One common method is shred or drill four holes through the entire drive. Another approach is to pry the platters apart to the extent that each platter is sufficiently warped or distorted to make it inoperable. It can also be taken to a professional for destruction. Some consumer electronics stores will do this as a courtesy for individual customers worried about what will happen to their old hard drive.

Complies with DoD, NSA & NIST Standard



DB-50PRO-E



HDB-20V-EB



DB-50PRO-EB



DB-50SSD-EB



DB-60HB-WH



Specification

- Destruction Method: Automated Hydraulic Pressure
- Application of pressure: 5 ton
- Operation System: 4 Holes through the Platters
- Destruction Cycle Time: approx. 10 Seconds
- MAX # of Continuous Operations: 200 units
- MAX # of Operations per day: 500 units
- Dimensions (W × H × D mm): 220x460x380mm

It's quick easy.



DB-50Pro is designed to conform the NSA guideline

DB-50Pro has HDD Destruction shafts that can make Four holes.

Destroys hard drive in 10 seconds by easy operation

Media and maximum numbers that can be processed

3.5-inch hard disk (thickness of 1.6 inches = 41 mm or less) —	_____	1 unit
2.5-inch hard disk	_____	1 unit
5-inch MO caddy (cartridge)	_____	1 piece
DVD caddy (cartridge)	_____	up to 2 pieces
Bare CD/DVD	_____	up to 5 pieces
5-inch MO disk	_____	up to 2 pieces
3.5-inch MO disk	_____	up to 2 pieces
3.5-inch floppy disk	_____	up to 5 pieces
Zip disk	_____	up to 2 pieces
Cell-phone	_____	up to 2 units
1-inch hard disk (optional)	_____	up to 4 units
1.8-inch hard disk (optional)	_____	up to 2 units

Part Names

Counter


Start switch

Stop switch

Power-switch


Media Slot (door)

Dust tray



circuit protector

Power input inlet



82 lbs (37Kg)

NITTOHZOHKI

manufactured by
 Nittoh Zohki Co., Ltd.
 585 Takashi, Mobara-shi, Chiba, 297-0029, JAPAN
 TEL: 81-475-26-5361
<http://www.nittoh.co.jp/>
crushbox@nittoh.co.jp